



Terminal Blocks

158-P02ECH381RH Series



KOBI CONN

Terminal Blocks


158-P02ECH381RH Series



P.C.B. LAYOUT



SECTION A-A



Dimensions: mm (In.)

MATERIAL SPECIFICATIONS

2	Solder pin:	Copper, Tin plated
1	Housing:	PBT, Green

SPECIFICATIONS

Rating:	300V 8A
Pitch:	3.81mm
Insulation withstand voltage:	AC 1000 V/min.
Insulation resistance:	1000MΩ at 500VDC
Temperature range:	-40°C ~ +130°C

Date Last Revised: 6-27-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300774

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

[158-P03ECH381RH](#) [158-P06ECH381RH](#) [158-P02ECH381RH](#)