

(2.00 mm) .0787"

YTW-12-10-S-6-300-215

YTW-26-02-T-5-250-050

YTW-20-03-G-Q-400-085

YTW SERIES

# HIGH-DENSITY BOARD STACKER

## SPECIFICATIONS

For complete specifications see [www.samtec.com/YTW](http://www.samtec.com/YTW)

**Insulator Material:**  
Black Liquid Crystal Polymer

**Terminal Material:**  
Phosphor Bronze

**Operating Temp Range:**  
-55 °C to +105 °C with Tin;  
-55 °C to +125 °C with Gold

**Plating:**

Sn or Au over  
50 μ" (1.27 μm) Ni

**RoHS Compliant:**

Yes

**Lead-Free Solderable:**

Wave only


## RECOGNITIONS

For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)





**Mates with:**  
YTQ, YTS, YTE

## OTHER SOLUTIONS



Paste In Hole (PIH) processing.  
Contact Samtec ASP Group.



**Note:**  
This Series is non-standard,  
non-returnable.

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.