

Europe (SME)

Products

SHARP Microelectronics Europe

- Product Groups
- System Solutions
- Support
- Where to Buy
- Press Room
- Jobs
- About Us
- Legal

LK460D3LA29 Sales and Technical Information

PRODUCT DETAIL INFORMATION		
Attribute Name	Attribute Data	
Active Area	1018.08 x 572.67 mm	
Backlight System	18 x CCFT	
Brightness	500 nits	
Contrast Ratio	3000:1	
Description	Signage Module featuring 176°symmetrical viewing cone, fast response time, and very high contrast ratio. Includes backlight inverter, anti-coating and 3H hard coating. Backlight is rated for 60,000 hours. For specifications on this part, see your local Sharp Representative. -glare	
Diagonal Size	46 inch (116.8 cm)	
Display Mode	Transmissive; Normally Black	
Family	LK460D3LA29	
Interface	LVDS: 1 billion colors	
Operating Temperature Range	0°C to 50°C	
Outline Dimensions	1083.0 x 624.7 x 53.4 mm	
Pixel Format	1920 x 1080	
Regional Exclusivity	LK460D3LA29 is not sold in the United States.	
Response Time	6 ms	
RoHS	Yes	
Status	New	
Storage Temperature Range	-25°C to 60°C	
Type	Full -HD	
Viewing Angle - 12 o clock	88 °	
Viewing Angle - 6 o clock	88 °	
Viewing Angle - side to side	176 °	