


HONEYWELL
PART NUMBER

311SM7602-H4

PRODUCT CODE

TZA2759

REV	DOCUMENT	CHANGED BY	CHECK
9	0038445	SSK 28APR08	BLR



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
2 - TERMINALS ARE PLATED FOR SOLDERING
3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

RELEASE NO.
PR-5576

REPLACES

CHARACTERISTICS

OPERATING FORCE -- 12 GRAM MAX

RELEASE FORCE-- -- 2 GRAM MIN

DIFFERENTIAL TRAVEL-- -- .015 MAX

OVERTRAVEL-- -- .026 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SPDT

30 VOLTS DC RATING

	SEA LEVEL	50,000 FT
INDUCTIVE	3 AMP	2.5 AMP
RESISTIVE	5 AMP	5 AMP

MAXIMUM INRUSH 24 AMP

APPROVALS	UL, CSA	4A, 250 VAC	UL	CS	BRAND	L119
-----------	---------	-------------	----	----	-------	------

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE	X	±
ONE PLACE	.X	±
TWO PLACE	.XX	±
THREE PLACE	.XXX	±
FOUR PLACE	.XXXX	±
ANGLES		±

THIRD ANGLE PROJECTION



DRAWN	VK	26FEB 08
CHECK	RJ	26FEB 08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		

RASTER

Honeywell

TITLE

SWITCH - BASIC

SIZE	TYPE	DRAWING NAME	REV
B	I	311SM7602-H4	9
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1