


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L	REV PER ECR 10-000722	22JAN10	JR	TM




AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED	2/0 AWG SOLID OR STRANDED

- 1 STAMP AMP 2/OW* APPROX AS SHOWN
- 2 TIN PLATE 0.00254[.000100] MIN THK EXT
PER ASTM B-545



50	LOOSE PIECE	36922
QTY	PACKAGING TYPE.	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170° MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHRUM 1/14/94		 Tyco Electronics Corporation Harrisburg, PA 17105-3608									
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A		DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK AJ KAUFMAN 1/19/94		NAME							
FOR APPLICATION		TOOLING ASSISTANCE CENTER		CIRCULAR MIL AREA:				0 PLC ± -		APVD JL MECKLEY 1/19/94		TERMINAL, RING TONGUE, SOLISTRAND -							
TOOLING INFORMATION		1-800-722-1111		60.6-76.3mm² [119,500-150,500] SOLID OR STRANDED				1 PLC ± -		2 PLC ± 0.20[.008]					PRODUCT SPEC				
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL		FINISH		WEIGHT		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO			
						COPPER PER ASTM B-152 ANNEALED		- 		-		A2		00779	C-36922		-		
CUSTOMER DRAWING										SCALE		2:1		SHEET		1 of 1		REV	L