



LB TYPE



C TYPE

- Suitable for wet locations when used with gasketed covers.
- Federal Specification W-C-586D / A-A 50563.
- Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b), Class I, Div. 2, (Suitable for use in Class I Zone 2 applications) 502.10, and 503.10.

Listed

Certified

FEATURES-SPECIFICATIONS

Applications

- Mogul fittings are for use with rigid and IMC raceways
- Use where standard conduit bodies do not provide adequate access and wiring area for the pulling of large and heavy conductors
- For right angle bends where splices, pulls and taps are needed in a weather-proof chamber

Features


- A raised dome cover permits additional wiring room
- Furnished with captive ss screws and gasket
- LBD, C and UB Series available with built-in cable-pulling rollers on sizes 1-1/2" and larger. Add -WR to catalog number. Example MOLBD-5-WR.

Material/Finish

- Cast iron moguls are hot dipped galvanized
- Aluminum moguls are of copper-free aluminum (less than 4/10 of 1%) with electrostatically applied powder coating

LB TYPE MOGUL CONDUIT BODY						
CATALOG NUMBER	KILLARK ALUM.	KILLARK IRON	HUB SIZE	LENGTH	ASSEMBLED HEIGHT	WIDTH
MOLBD-1	MOLBD-1M		1/2"	5" (127)	2-5/16" (59)	1-5/16" (33)
MOLBD-2	MOLBD-2M		3/4"	6-1/4" (159)	2-5/8" (67)	1-9/16" (40)
MOLBD-3	MOLBD-3M		1"	9-5/8" (244)	3-5/8" (92)	2-1/2" (64)
MOLBD-4	MOLBD-4M		1-1/4"	9-5/8" (244)	3-5/8" (92)	2-1/2" (64)
MOLBD-5	MOLBD-5M		1-1/2"	14-7/16" (367)	5-5/8" (143)	3" (76)
MOLBD-6	MOLBD-6M		2"	14-7/16" (367)	5-5/8" (143)	3" (76)
MOLBD-7	MOLBD-7M		2-1/2"	22" (559)	7-1/2" (191)	4-1/2" (114)
MOLBD-8	MOLBD-8M		3"	22" (559)	7-1/2" (191)	4-1/2" (114)
MOLBD-9	MOLBD-9M		3-1/2"	28-1/2" (724)	9-1/4" (235)	5-1/2" (140)
MOLBD-0	MOLBD-0M		4"	28-1/2" (724)	9-1/4" (235)	5-1/2" (140)

NOTE - For built-in cable rollers (on sizes 1-1/2" and larger), add -WR to catalog number. Example: MOLBD-5WR.



C TYPE MOGUL CONDUIT BODY						
CATALOG NUMBER	KILLARK ALUM.	KILLARK IRON	HUB SIZE	LENGTH	ASSEMBLED HEIGHT	WIDTH
MOC-3	MOC-3M		1"	12" (305)	3" (76)	2-5/8" (67)
MOC-4	MOC-4M		1-1/4"	12-1/16" (306)	3-5/16" (84)	2-5/8" (67)
MOC-5	MOC-5M		1-1/2"	18-1/8" (460)	3-7/8" (98)	3-3/16" (81)
MOC-6	MOC-6M		2"	18-1/16" (459)	4-7/16" (113)	3-3/16" (81)
MOC-7	MOC-7M		2-1/2"	27-1/16" (689)	5-3/16" (132)	4-11/16" (119)
MOC-8	MOC-8M		3"	27-1/4" (692)	5-15/16" (151)	4-11/16" (119)
MOC-9	MOC-9M		3-1/2"	35-3/8" (899)	7-3/16" (183)	5-11/16" (144)
MOC-0	MOC-0M		4"	35-7/16" (900)	7-9/16" (192)	5-11/16" (144)

NOTE - For built-in cable rollers (on sizes 1-1/2" and larger), add -WR to catalog number. Example: MOLBD-5WR.



KILLARK®