

ESHF-125-01-L-D-SM-LC

ESHF-105-01-L-D-SM

EHF-125-01-L-D-SM-LC

SHF, ESHF, EHF, ECF SERIES

SHROUDED & EJECTOR IDC HEADER

FFSD*, FFTP

EHF — **1** **NO. PINS PER ROW** — **01** — **PLATING OPTION** — **D** — **TAIL OPTION** — **OTHER OPTION**

04, 05, 08, 10, 13, 17, 20, 25
(Standard sizes)

-F
= Gold flash on post,
Matte Tin on tail

-L
= 10μ" (0,25 μm)
Gold on post,
Matte Tin on tail

-SM
= Surface Mount

-RA
= Right Angle

Leave blank for Through-Hole version

-“XX”
= Polarized Position
(-RA not available)

-LC
= Locking Clip
(-SM only)
(Manual placement required)

-K
= (7,50 mm) .295" DIA
Polyimide Film Pick
& Place Pad

-P
= Pick & Place Pad
(-SM only)

-TR
= Tape & Reel
Packaging
(-LC not available)

Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.