


Use VDC SLIPSTREAM — Freephone 08000 747 VDC

Call this number for straightforward stock-coded orders only — there is no technical support on this number




pre-made monitor and pc cables **4**

Stock code	Description
104-048	VGA male — female 2m
104-222	VGA male — female 3m
104-224	VGA male — female 6m
104-226	VGA male — female 10m
104-228	VGA male — female 20m
104-230	VGA male — female 30m
104-232	VGA male — female 50m
104-234	VGA male — male 2m
104-236	VGA male — male 3m
104-238	VGA male — male 6m
104-240	VGA male — male 10m
104-242	VGA male — male 20m
104-244	VGA male — male 30m
104-246	VGA male — male 50m
104-150	Monitor adaptor
104-152	5 pin DIN extension 3m
104-154	5 pin DIN extension 6m
104-156	5 pin DIN extension 10m
104-158	PS2 extension 3m
104-160	PS2 extension 5m
104-162	PS2 extension 10m
104-164	ADB extension 5m
104-166	ADB extension 7.5m
104-168	ADB extension 15m
104-180	9D extension 3m
104-182	9D extension 6m
104-184	9D extension 10m
104-186	VGA 2 way switch
104-188	VGA 4 way DA
104-050	VGA — 4 x BNC 2m
104-052	VGA — 5 x BNC 2m
104-054	D sub male — female 2m
104-056	D sub — 3 x BNC 2m
104-058	D sub — 4 x BNC 2m



A range of high quality moulded cables manufactured using multicore video cable. Connector types are either 15 pole D sub high density types (VGA/SVGA) or standard 15 pole D sub types.


manufacturing pre-made data cables



77

Stock code	Length
104-060	0.5m
104-062	1m
104-064	2m
104-066	3m
104-068	5m
104-070	10m
104-072	15m
104-074	20m

RS422 remote cables **5**



9 pole D sub male to male wired using 2 pair individually screened low capacitance cable. Industry standard for remotes and machine control. The low capacitance cable allows long lengths to be run without problems.

tel **0171 700 2777**
email **sales@vdctrading.com**

fax **0171 700 3888**
web **http://www.vdctrading.com**