

CAB CAB PC 403018 T



Sample photo

Order symbol: CAB PC 403018 T
Product nbr: 8113050
Description: Cabinet, PC
Remarks: Latches on the long side

EAN:	6418074020215
El. number:	
Finland:	3424164
Denmark:	8212020252
Italy:	7822040
Sweden:	2539945
Norway:	

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		Length	Width	Height	Rating:
mm:		400	300	180	Ingress Protection (EN 60529): IP 65
inch:		15.7	11.8	7.1	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Smoked grey			Flammability Rating (UL 746 C 5): UL 746C 5V
Gasket material:		EPDM			Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:					UL Type: UL TYPE 1, 4, 4X, 12, 13
Short term:		-40 ... 120 °C			Certificates:
Continuous:		-40 ... 80 °C			Germanischer Lloyd (GL)
Short term:		-40 ... 250 °F			Underwriters Laboratories
Continuous:		-40 ... 175 °F			Fimko
Accessories:					Lloyds Register of Shipping (LR)
EKIV 43		Mounting plate			Europe EN 62208: 2003
EKIV 43 PL		Mounting plate, Plastic			UL Canada
EKIV 27		DIN-35 Mounting rail			Gost R
DS3527OE1		DIN-35 Mounting rail			
EKIV 37		DIN-35 Mounting rail			
DS3537OE1		DIN-35 Mounting rail			
FP A 43		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 43		Front plate			
FP 12x2-43		Front plate			
FP 12x3-43		Front plate			
DRF 43/44		DIN rail frame set			

