

Search For

enter search text

Part Number

Home> 5700100723F

Part Number: **5700100723F**

General Description	
Series	570
Configuration	2 mm Lens
Description	2 mm Tri -Level CBI O -G-Y
Package Options	Bulk Packaging
Sizes	2mm
Lamp Type	Tri -Level Housing
Viewing	Right Angle
Polarity	Cathode Left
Lens Style	Tinted, Diffused
Viewing Angle	70
LED Centerline	1.78mm

Absolute Maximum Ratings (Ta = 25Â°)	
Solder Temperature	260 for 5 secs
Operating Temperature	-40 to 85
Storage Temperature	-40 to 85

Operating Characteristics			
	LED Position: 1	LED Position: 2	LED Position: 3
Color	Orange	Green	Yellow
LED Type	Standard Efficiency	Standard Efficiency	Standard Efficiency
Peak Wave Length	607	565	590
Luminous Intensity Min	5	5	5
Luminous Intensity Typical	10	10	8
Forward Voltage Typical	2.05	2.2	2.1
Forward Voltage Max		2.5	2.5
Power Dissipation Max	105mW	105mW	105mW



5700100723F

check stock



This is a
RoHS Compliant Product

To learn more click here