

Configuration details for Vega power supply V600D2K

Part number	V600D2K
Product description	V6FSS 12/12H3/3S 5E2S 24D5S
Total connected power	636 W
Total available power	650 W
Agency approvals	C-UL-US, CE.
Input type	AC
Cooling	Forward air fan - end mount
Input	Screw
Filter	1.50 milliamps maximum leakage current
Primary option	None
Dimensions	Length: 268.4mm, Width: 126.5mm, Height: 62.8mm

Module	D5	E2	H3/3
Output 1	24V/11A	5V/60A	12V/2A
Output 2	-	-	12V/4A
Option	None	None	None
Connection	Screw	Screw	Screw

The view shown is of the output end of the supply.