


**Model 3276 & 4513**  
**Miniature Banana Plug with Threaded Stud**

| Model       | "X" Dimension |
|-------------|---------------|
| <b>3276</b> | .23" (5,8mm)  |
| <b>4513</b> | .48" (12,2mm) |

Minimum Panel Thickness is 0.030" (0.76mm)

**Features**

- Threaded stud enables fast and easy mounting to panels.
- Solder turret allows wire attachment.
- Miniature banana plug features gold plated Beryllium Copper for long insertion life and low contact resistance.

**Materials**

Miniature Banana Plug:

Spring: Beryllium Copper, Gold Plated

Body: Brass, Gold Plated

Hex Nut: 4-40 Nut, Brass, Nickel Plated

**Ratings**

Operating Voltage: 2500 VDC


Current: 5 Amperes Max.

**Ordering Information**

Model 3276

Model 4513

Parts are packaged ten per bag, unassembled.



**USA:** Sales: 800-490-2361  
Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)  
Fax: 425-446-5844

**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500  
**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.