



PRODUCT NUMBER  
10098870-1102LF



0.35±0.03 TYP  
⊕ ∅ 0.05 (S) A B

1.80±0.03 TYP  
⊕ ∅ 0.05 (S) A B

B

16.80

P.C.B. EDGE

5.00

4.60

B1

A1

5.00

4.60

0.80

0.40

FULL RADIUS

∅ 1.55±0.04

2.51

5.18

A

12.00±0.05

# NOTES:

- CONTACT MATERIAL: COPPER ALLOY  
PLATING:  
UNDERPLATING: NICKEL PLATING OVER ALL THICKNESS 1.27µm MIN.  
CONTACT AREA: GOLD PLATING (SEE TABLE)  
HOUSING MATERIAL: HIGH-TEMP THERMOPLASTIC, COLOR: BLACK  
FLAME RETARDANT PER UL 94V-0
- PRODUCT SPECIFICATION: GS-12-548
- APPLICATION SPECIFICATION: GS-20-124
- DATE CODE PRINTED APPROXIMATELY AS SHOWN.
- PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.



R/A SMT 0.80mm PITCH  
MINI-SAS CONNECTOR  
catalog no

dwg no  
10098870

Rev.  
C

CUSTOMER sheet 2 of 2