

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35725-3910](#)
Status: **Active**
Overview: [Quick-Disconnect Terminals](#)
Description: Quick Disconnect, Female, Piggyback Type, for 14-18 AWG (2.00-0.80mm²), Metal Strip, Tab 6.35 x 0.81mm, Post Tin Plating

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-35725-003 \(PDF\)](#)

Agency Certification

UL E92853

General

Product Family Quick Disconnects
Series [35725](#)
Crimp Quality Equipment Yes
Insulated No
Overview [Quick-Disconnect Terminals](#)
Product Name N/A
Type Quick Disconnect
UPC 800753199590

Physical

Barrel Type Open
Gender Female
Glow-Wire Compliant No
Insulation None
Lock to Mating Part None
Material - Metal Brass
Net Weight 1.027/g
Orientation Piggyback
Packaging Type Reel
Polarized to Mating Part No
Tab Thickness 0.81mm
Tab Width 6.35mm
Temperature Range - Operating -40°C to +85°C
Wire Insulation Diameter 3.60mm max.
Wire Size AWG 14, 16, 18
Wire Size mm² 0.80 - 2.00


Electrical

Voltage - Maximum N/A

Material Info

Reference - Drawing Numbers

Product Specification PS-35725-003
Sales Drawing SD-35725-*910



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[35725Series](#)

Use With
6.35mm Tab

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35725-3910](#)