


REV.	DATE	DESCRIPTION
NC	12/20/07	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
8						DRAWN	G.R.S.	12/20/07										
7						CHECKED												
6	HEX NUT	BRASS	GOLD	1			ISSUED				PART DESCRIPTION							
5	LOCK WASHER	BRASS	GOLD	1							SMA REVERSE POLARITY BULKHEAD JACK TO JACK ADAPTER							
4	GASKET	SILICON	RED	1							PART NO.							
3	CONTACT PIN	BRASS	GOLD	1			SHEET	1 OF 1			132170-10RP-RP							
2	INSULATOR	TEFLON	NATURAL	1			CAD FILE			DWG. NO.		132170-10RP-RP.DWG	REV.	NC	SIZE	A	SCALE	NA
1	BODY	BRASS	GOLD	1		C:/132/132170-10RP-RP.DWG												
	DESCRIPTION	MATERIAL	FINISH	QTY														