



- Superior adhesive for long term reliability
- 2-up mount configuration speeds liner removal and installation
- 4-way cable tie entry makes part orientation fast and easy
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Used with *PANDUIT*® cable ties for a complete wire routing solution

‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

Part Number: ABM1M-A-C
Product Family: 4-Way Adhesive Backed Cable Tie Mounts
Product Line: Adhesive Backed

Product Line: Adhesive Mounts

RoHS Compliancy Status: Compliant

Part Description: 4-Way Adhesive Backed Cable Tie Mount

Product Type: Cable Tie Mounts - Adhesive Backed

Material: Nylon 6.6

Color: White

UL Recognized: E136577

Height (In.):	.16
Height (mm):	4.0
Length (In.):	.50
Length (mm):	12.7
Width (In.):	.50
Width (mm):	12.7
Adhesive Type:	Rubber
CE Compliant:	CT-ACC1 / 10.96
Environment:	Indoors
Max. Static Load (g):	59
Max. Static Load (Lbs.):	.13
Mounting Method:	Adhesive Backed
Std. Pkg. UOM:	PK
Used With Cable Ties:	M
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100