


Axial Lead and Cartridge Fuses

Subminiature Glass Body

2AG Fast-Acting Fuse 224/225/288/289 Series



The 2AG Fast-Acting fuses are available in cartridge form or with axial leads. Axial leaded fuses are board washable. 2AG fuses provide the same performance characteristics as their 3AG counterpart, while occupying one-third the space. Sleeved fuses are available.

ELECTRICAL CHARACTERISTICS:

% of Ampere Rating	Opening Time
110%	4 hours, Minimum
135%	1 hour, Maximum
200%	1 second, Maximum

AGENCY APPROVALS: All ratings are Listed by UL and Certified by CSA. 1 through 10 amperes approved by METI.

AGENCY FILE NUMBERS: UL E10480, CSA LR 29862.

FUSES TO MIL SPEC: 224 and 225 Series 1/8 through 7 amperes are available to DSCC Drawing #87108. To order, change 224 to 289 or 225 to 288. See page 361.

INTERRUPTING RATINGS:

0.1–10A	10,000 amperes at 125 VAC
0.1–1A	35 amperes at 250 VAC
1.5–3.5A	100 amperes at 250 VAC

PACKAGING OPTIONS: 224 Series available on Tape and Reel per EIA-296. For 1500 pieces per reel, add packaging suffix DRT1. See page 8 for pitch Dimensions. 224, 225 series available in bulk packaging. For 1000 pieces bulk add packaging suffix M.

See Page 289 for Soldering Parameters and Environmental and Physical specifications.

PATENTED

ORDERING INFORMATION:

Cartridge Catalog Number	Axial Lead Catalog Number	Ampere Rating	Voltage Rating	Nominal Resistance Cold Ohms	Nominal Melting I ² t A ² Sec.
225.100	224.100	1/10	250	6.15	0.000750
225.125	224.125	1/8	250	3.90	0.00286
225.250	224.250	1/4	250	1.15	0.0300
225.375	224.375	3/8	250	0.395	0.171
225.500	224.500	1/2	250	0.265	0.365
225.750	224.750	3/4	250	0.152	1.05
225 001	224 001	1	250	0.102	2.22
225 01.5	224 01.5	1½	250	0.0705	0.800
225 002	224 002	2	250	0.0490	1.50
225 02.5	224 02.5	2½	250	0.0365	2.68
225 003	224 003	3	250	0.0310	4.62
225 03.5	224 03.5	3½	250	0.0258	6.70
225 004	224 004	4	125	0.0233	9.40
225 005	224 005	5	125	0.0179	17.00
225 006	224 006	6	125	0.0147	22.1
225 007	224 007	7	125	0.0123	40.0
225 008	224 008	8	125	0.0100	56.0
225 010	224 010	10	125	0.00675	116.0

2AG Special 350V

Fast-Acting Fuse



The **220 007** subminiature fuse is intended for fluorescent lighting ballast protection or similar applications up to 350V.

AXIAL LEAD PART NUMBER: 220 007 (ampere rating of 3A).

DIMENSIONS: Same as 224 Series.

ELECTRICAL CHARACTERISTICS: Same as 224 Series.

INTERRUPTING RATING: 100 amperes at 350 VAC.


PATENTED

Contact Littelfuse concerning other ampere ratings.



225 000 Series

224 000 Series



Axial Lead Material: Solder coated copper.

Average Time Current Curves

