



+ TERMINALS & SPLICES

QUICK DISCONNECTS



Obsolete

TE CONNECTIVITY (TE)

.250 FASTON REC.

FASTON | 250

880045-1

TE Internal Number: 880045-1

EU RoHS Compliant

EU ELV Compliant

Terminal Type Receptacle

Wire Size (AWG) 17 – 13

Wire Size (mm²) 1 – 2.5

Mating Tab Width 6.35 mm [.25 in]

Mating Tab Thickness .81 mm [.032 in]

DOCUMENTATION

No documentation available.

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Terminates To Wire & Cable

FASTON Yes

Insulated Wire Support Yes

Disconnect Type Quick Disconnect Pin

Insertion Force Normal

Insulated No

Wire/Cable Type Discrete Wire

Wire/Cable Composition Stranded

Body Features

Fully Insulated Yes

Plating Material Unplated

Contact Features

Terminal Type Receptacle

Terminal Orientation Straight

Barrel Type Open

Crimp Type F-Crimp

Dimensions

Wire Size (AWG) 17 – 13

Wire Size (mm²) 1 – 2.5

Mating Tab Width 6.35 mm [.25 in]

Mating Tab Thickness .81 mm [.032 in]

Accepts Wire Insulation Diameter Range 3 – 4 mm [.118 – .157 in]

Overall Length 17.1 mm [.673 in]

Packaging Features

Packaging Method Reel

Packaging Quantity 10000

PRODUCT COMPLIANCE



Statement of Compliance

[**Statement of Compliance**](#)

PDF
