


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	5	Vdc
OPERATING VOLTAGE RANGE	3 ~ 7	Vdc
RATED CURRENT (MAX)	30	mA
MINIMUM SPL @ 10 cm.	85	dBA
RESONANT FREQUENCY	2,300±300	Hz
TONE OR PULSE RATE	CONTINUOUS	0 PULSE PER SECOND
OPERATING TEMPERATURE	-20 ~ +70	°C
STORAGE TEMPERATURE	-30 ~ +80	°C
HOUSING MATERIAL	NORYL	—
TERMINAL MATERIAL	TIN-PLATED COPPER	—
WEIGHT	2	grams

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	6/23/99	
A	ADDED ELECTRICAL SPECIFICATION	6/7/02	S. J.
B	REVISED TO NEW TEMPLATE	10/13/03	R. W.
C	ADDED NOTES 3 & 4	10/13/03	R. W.
D	REVISED TO NEW TEMPLATE	5/5/04	R. W.
E	REVISED DIMENSION SIZE AND STYLE	11/23/05	B. R.



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. POSITIVE LEAD IS LONGER LEAD.
4. PART INFORMATION IS ON THE SAME SIDE AS THE POSITIVE LEAD.

FILE NAME
AI-155.DWG

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN TMM	6/99
APPROVED S. J.	6/99
E. P.	5/04

DO NOT SCALE DRAWING



projects®
unlimited

Dayton, Ohio

AUDIO INDICATOR
AI-155

SIZE
A

DRAWING NO.
AI-155

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AI-155](#)