

ALLIGATOR CLIPS



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5

Miniature Alligator Clip

Retail Part No.	Bulk Part No.	N.S.N. Part Number	Fig. No.	Description	Current Rating	Body	Connection Type	Jaw Opening Inch(mm)
	33-077-BU	5999-00-060-8996	1	Mini Alligator Clip	5 Amps	Nickel Plated Steel	Solder	1/2" (12.700)

Can be used with GC Electronics 26-18 AWG Hook-Up Wire (See Wire Section p422-423)

Alligator Clip w/Vinyl Sleeve

Retail Part No.	Bulk Part No.	N.S.N. Part Number	Fig. No.	Description	Current Rating	Body	Connection Type	Jaw Opening Inch(mm)
	33-075-BU	5999-00-880-5534	2	Red Handle Clip	5 Amps	Nickel Plated Steel	Solder/Screw	5/16" (7.938)
	33-076-BU	5999-00-235-0214	2	Black Handle Clip	5 Amps	Nickel Plated Steel	Solder/Screw	5/16" (7.938)

Can be used with GC Electronics 26-18 AWG Hook-Up Wire (See Wire Section p422-423)

Alligator Clips

Retail Part No.	Bulk Part No.	N.S.N. Part Number	Fig. No.	Description	Current Rating	Body	Connection Type	Jaw Opening Inch(mm)
	33-078-BU		3	Alligator Clip	5 Amps	Nickel Plated Steel	Solder/Banana	3/8" (9.525)
	33-079-BU		4	Alligator Clip	5 Amps	Nickel Plated Steel	Screw/Banana	3/8" (9.525)

Can be used with GC Electronics 26-18 AWG Hook-Up Wire (See Wire Section p422-423)

Alligator Clip Insulator

Retail Part No.	Bulk Part No.	Figure Number	Description	Jaw Opening Inch(mm)
	33-081-BU	5	Red-Flexible Molded Vinyl Insulator that Fits All Standard Sizes	N/A
	33-082-BU	5	Black-Flexible Molded Vinyl Insulator that Fits All Standard Sizes	N/A

For use with above Alligator Clips

BINDING POSTS



Fig. 6



Fig. 7



Fig. 8

Heavy Duty Binding Posts

Retail Part No.	Bulk Part No.	N.S.N. Part Number	Fig. No.	Description	Current Rating	Body	Connection Type
	33-278-BU		6	Red Molded Nylon per MIL-P-20693A	30 Amps	Nickel Plated Brass	Banana/Tip Plug,Lug,
	33-280-BU		6	Black Molded Nylon per MIL-P-20693A	30 Amps	Nickel Plated Brass	Alligator Clip, Wire

Use 14 AWG or larger

Dual Binding Post

Retail Part No.	Bulk Part No.	N.S.N. Part Number	Fig. No.	Description	Current Rating	Body	Connection Type
	33-292-BU		7	Molded Nylon per MIL-P-20693A	15 Amps	Nickel Plated Brass	Banana Plugs

Use with GC Electronics Part No. 14-210-9Hxx wire

BNC Male to Dual Binding Post

Retail Part No.	Bulk Part No.	N.S.N. Part No.	Fig. No.	Description	Current Rating	Body	Connection Type
33-1192	33-1192-BU		8	BNC Male to Dual Binding Posts, Stackable	N/A	Nickel Plated Brass	Banana

Use with GC Electronics 18 AWG or larger wire such as Part Nos. 14-210, 14-212, 14-418