



FEATURES:

- Features flex boots for insulation protection.
- Alligators are nickel plated for tarnish resistance.
- Alligator clip has .187" (4.75mm) max. jaw opening.
- Ideal for use as a temporary wire.

MATERIALS:

Alligator:

Body: Steel, Nickel Plated

Spring: Stainless Steel

Flex Boot: Vinyl

Wire:

(Model 1236) 20 AWG, Stranding: 41 x 36 tinned copper, PVC Insulation, .087" (2.21 mm) O.D.

Marking: "POMONA 1236-XX"

(Model MG-B) 18 AWG, Stranding: 65 x 36 tinned copper, PVC Insulation, .144" (3.66 mm) O.D.

Marking: "POMONA MG-B-XX"

RATINGS:

Operating Voltage: 30VAC/60VDC MAX.

Operating Temperature: +50°C (+122°F)

Current: 5 Amperes

ORDERING INFORMATION: Model 1236-XX-*, Model MG-B-XX-*

XX = Length in inches

Standard Lengths: 4" (10.16mm), 8" (20.32mm), 12" (30.48mm), 24" (60.96mm), 36" (91.44mm), 48" (121.92mm) & 60" (152.40mm). Additional lengths can be quoted upon request.

* = Color of Flex Boot and Wire, -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA