

C-Series





The C-Series toggle switches are single pole switches with ratings up to 20 amps and 1 1/2 horsepower. These switches are available with plated brass toggles and bushings.

- Specifications
- Certifications*: UL, CSA
 - Dielectric Strength: 1,000V (minimum)
 - Insulation Resistance: 100 Megohms (minimum)
 - Base Material: Polyarylether
 - Actuator Material: Brass/Nickel Plate
 - Bushing Material: Brass/Nickel Plate

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



SERIES

C

SINGLE POLE TOGGLE

CIRCUIT

A

ON-NONE-OFF
ON-NONE-ON

RATING

20

5A 250VAC
10A 125VAC
1/2HP 125-250VAC
10A 250VAC
20A 125VAC
1 1/2HP 125-250VAC

TERMINATION

1

.250TAB (QC)

TOGGLE STYLE

73

TOGGLE BUSHING SUFFIX NEOPRENE SEAL

.406 .343 52 57

.687 .465 73 78

NOTES:
Shading indicates standard configurations.