






MATERIAL NUMBER	OLD PART NUMBER
120114-0065	BTY801P-FBB



ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	NYLON	BLACK
2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	O-RING	NITRILE	RED
4	RECEPTACLE SHELL	BRASS	NICKEL PLATED
5	HOUSING	PBT	YELLOW
6	LABEL	ABS	WHITE
7	LENS	NYLON	CLEAR
8	INSERT	PVC	YELLOW
9	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
10	RECEPTACLE SHELL	BRASS	NICKEL PLATED

VOLTAGE RATING	10-30 VDC
AMPERAGE RATING PER PORT	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 90°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

RELEASED DRAWING EC NO: WEU2010-0067 DRWN: LHARTMAN 8/25/09 CHKD: BWOODMAN2009/08/27 APPR: JFMURPHY 2009/08/28 A	DESCRIPTION REV	QUALITY SYMBOL =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY LHARTMAN	DATE 2009/08/25	TITLE MICRO-CHANGE MPIS 8 PORT TOP MOUNT PNP MINI 12 POLE MALE			
			4 PLACES	±----	±----	CHECKED BY BWOODMAN	DATE 2009/08/27				
			3 PLACES	±----	±----	APPROVED BY JFMURPHY	DATE 2009/08/27	molex MOLEX INCORPORATED			
			2 PLACES	±----	±.01	MATERIAL NO. SEE CHART					DOCUMENT NO. SD-120114-010
			1 PLACE	±0.3	±----	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
			ANGULAR ±----°								
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1201140065