

重量用
キャスター

キャスター

双輪
キャスター緩衝器付
キャスターアジャスター付
キャスター

戸車

ボール
キャスターモニター
アームレバーブ
アジャスタードアストッパー
DOOR STOPPERS

K-900A



K-900A-S1



K-900A-S2

K-900A
鉄製

特徴 Feature

- 小型で軽量なため広範囲に利用できます。
- 側面取付けタイプ
- 床面に多少凸凹があっても確実にロックできます。
- Small-sized and lightweight and widely used.
- Side attachment type.
- Can be locked securely even if floor is a little uneven.

仕様 ● 材質: 本体/熱間圧延鋼板(SPHC)

接地部/ゴム

- 表面仕上: 亜鉛めっきクロメート処理(MFZn-C)
- ドア・扉・運搬器具・事務用機器・その他移動防止用
- 標準品・・・納期お問合せください
- ロック解除の状態で床面とベースゴムの間隔を約25~30mmに取付けてください。
- 取付け穴は左・右5個ありますので適当な穴を選び、ボルト・ねじなどで取付けてください。

Specifications ● Material: Main body: Hot rolled steel plate (SPHC)
Ground contact part: Rubber

● Finish: Zinc plating chromate treatment (MFZn-C)


Specific- ● For stoppers for door, gate door, use carrying and office and other equipment

Remarks ● Set up so that there is a gap of 25mm to 30mm between the floor and the base rubber when the pedal is in the unlocked position.


● Installing holes are left and right five each.

Use appropriate holes and fix with bolts and screws.

[K-900A-S1]



[K-900A-S2]



商品番号 Product No.	RoHS 10 2D/3D	CAD	製品質量(g) Mass	コード Code	単価 Price	量販価格 Bulk Price	
						数量 Quantity	単価 Price
K-900A	●	●	450	30501	¥1,550	12個~	¥1,504
K-900A-S1	●			30502	¥280	30個~	¥272
K-900A-S2	●			30503	¥280	30個~	¥272

● : RoHS10指令対応品 ▲ : RoHS10指令に対応可能です。

※大量のご注文は更にお安くなります。