

Panel mounting frames - VS-08-A-RJ45/LP-1-IP67-BK - 1658655

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



RJ45 panel mounting frame, IP67, for PCB connection, for square panel cutout, with grommet, without mounting screws, color: black



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	5 pc
GTIN	 4 046356 163194
GTIN	4046356163194
Weight per Piece (excluding packing)	5.070 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Mechanical characteristics

Number of slots	1
Degree of pollution	2
Weight	0.96 g
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (assembly)	-5 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Material data

Panel mounting frames - VS-08-A-RJ45/LP-1-IP67-BK - 1658655

Technical data

Material data

Housing material	PA
Width	32.5 mm
Height	32.5 mm
Depth	20 mm

Electrical characteristics

Degree of pollution	2
---------------------	---

Standards and Regulations

Flammability rating according to UL 94	V0
--	----


Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings


Panel mounting frames - VS-08-A-RJ45/LP-1-IP67-BK - 1658655

Dimensional drawing



Panel mounting frames - VS-08-A-RJ45/LP-1-IP67-BK - 1658655


Drilling diagram



Drilling plan for VS-08-BU-RJ45-6/LH-1

Panel mounting frames - VS-08-A-RJ45/LP-1-IP67-BK - 1658655

Dimensional drawing



Mounting cutout

Classifications

eCl@ss

eCl@ss 10.0.1	27440210
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27261200

Panel mounting frames - VS-08-A-RJ45/LP-1-IP67-BK - 1658655

Classifications

eCl@ss

eCl@ss 7.0	27440210
eCl@ss 8.0	27440210
eCl@ss 9.0	27440210

ETIM

ETIM 2.0	EC000764
ETIM 3.0	EC001121
ETIM 4.0	EC002310
ETIM 5.0	EC002310
ETIM 6.0	EC002310
ETIM 7.0	EC002310

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121421
UNSPSC 18.0	39121421
UNSPSC 19.0	39121421
UNSPSC 20.0	39121421
UNSPSC 21.0	39121421

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

Panel mounting frames - VS-08-A-RJ45/LP-1-IP67-BK - 1658655

Accessories

Accessories

Female insert

RJ45 PCB connectors - VS-08-BU-RJ45-6/LH-1 - 1653087



RJ45 PCB connectors, type: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), connection method: Solder connection

Protective cover

Protective covers - VS-08-SD-F-BK - 1658066



Protective cover, IP67, flat design, to cover the contact insert in the panel mounting frame, color: black