



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	OWN
						APVD
			C2	REVISED PER ECO-11-004917	11MAR11	RK



AMP
WIRE RANGE

8 AWG
SOLID OR STRANDED

- 1 STAMP AMP 8* APPROX AS SHOWN
- 2 COPPER PR ASTM B-152, ANNEALED
- 3 NICKEL PLATE 0.00762 [0.000300] MIN THK PER QQ-N-290.



323165
PART NO.

MAX. RECOMMENDED OPERATING TEMPERATURE: 343°C. MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-19-93	TE Connectivity TERMINAL, RING TONGUE, HEAT RESISTANT, STRATO-THERM						
			CHK DA PATTERSON 4-19-93							
VOLTAGE RATING: N/A	DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD JL MECKLEY 4-19-93	NAME						
CIRCULAR MIL AREA: 6.64-10.50mm ² [13,100-20,800] SOLID OR STRANDED		0 PLC ± -	PRODUCT SPEC	SIZE A2						
		1 PLC ± -	—							
		2 PLC ± -	APPLICATION SPEC							
		3 PLC ± -	—							
		4 PLC ± -	—							
MATERIAL	FINISH	WEIGHT	CAGE CODE 00779				DRAWING NO C=323165		RESTRICTED TO	
		—	CUSTOMER DRAWING				SCALE 8:1	SHEET 1 of 1	REV C2	