

Section Links

A045 | A040 | A095 | A090 | A195 | A190 | A080 | A085 | A087 | A200 | A070 | A210 | **A300** | A315 | A089 | A125 | A105 | A205

Product Details

A300 Light Duty Low Profile Fixed Stud Levelling Foot Stainless Steel Stud and Base with Inset Nitrile Rubber Pad

Materials Base - Stainless Steel type 303 with Inset Nitrile Rubber Pad
Stud - Stainless Steel type 303



Part No.	Thread Size D1 (mm)	Thread Length L (mm)	Base Diameter D2 (mm)	Overall Height H (mm)	Pad Thickness (mm)	Maximum Recommended Load (kg)
A300/001	M8	40	40	52	3	450
A300/002	M8	60	40	72	3	450
A300/003	M10	40	40	52	3	600
A300/004	M10	60	40	72	3	600
A300/005	M10	80	40	92	3	600
A300/009	M8	40	50	54	3	450
A300/010	M8	60	50	74	3	450
A300/011	M10	40	50	54	3	600
A300/012	M10	60	50	74	3	600
A300/013	M10	80	50	94	3	600
A300/014	M12	50	50	65	3	750
A300/015	M12	75	50	90	3	750
A300/016	M12	100	50	115	3	750

Dimensions are approximate

