

Twist-Lock® Devices

30 Ampere, 125/250 Volts and 3Ø 250 Volts AC

3 Pole, 4 Wire Grounding

Insulgrip® Plugs and Flanged Inlets


Fed.Spec.



30A 125/250V
NEMA L14-30P
UL/CSA
2 (2) HP



30A 3Ø 250V AC
NEMA L15-30P
UL/CSA
3 HP

**HBL2711SW****HBL2711S****HBL2711****HBL2715SW****HBL2715****Plugs****Watertight Safety-Shroud®****IP66** SUITABILITY

Description	Cord Dia.	Catalog Numbers	
Black Valox® housing, white Valox® clamps.	.35"-1.15" (9-29)	HBL2711SW	HBL2721SW

Safety-Shroud**IP20** SUITABILITY

Description	Cord Dia.	Catalog Numbers	
Black and white nylon body, white Valox® shroud. Can be used with the Insulgrip Connector Bodies.	.35"-1.15" (9-29)	HBL2711S	HBL2721S

Accessories on page B-40.

Insulgrip**IP20** SUITABILITY

Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.35"-1.15" (9-29)	HBL2711	HBL2721
Corrosion resistant, yellow nylon.	.35"-1.15" (9-29)	HBL27CM11	HBL27CM21
All black nylon.	.35"-1.15" (9-29)	HBL2711BK	-

Accessories on page B-53.

Flanged Inlets**Watertight Safety-Shroud****IP66** SUITABILITY

Description	Catalog Numbers	
Gray Valox® housing and flange.	HBL2715SW	HBL2725SW

Accessories on page B-54.

Insulgrip**IP20** SUITABILITY

Description	Catalog Numbers	
Nylon casing, back wired.	HBL2715	HBL2725

Accessories on page B-52.

Notes: For technical information on Twist-Lock® and Watertight Safety-Shroud Devices see pages B-69 and 70.

HBLMITL - For use with Watertight Safety-Shroud receptacles, see page B-39.



Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.