


Terminal Blocks

158-P02EK381V Series

KOBICONN

Terminal Blocks



Dimensions: mm (IN.)

SPECIFICATIONS

Rating:	300V 12A
PITCH:	3.81mm
Insulation withstands voltage:	AC 1500V/Min
Insulation resistance:	500MΩ or more at DC500V
Temperature range:	-40°C~+105°C
Screw torque value:	2kgf-cm
Electric wire:	AWG 16~22

MATERIAL SPECIFICATIONS

Wire cage (4):	brass M2/Ni plated
Screw (3):	steel M2/Zn plated
Solder pin (2):	copper tin plated
Housing (1):	PA66 green

Date Last Revised: 6-24-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300759

158-P02EK381V Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

[158-P02EK381V12](#) [158-P02EK381V7](#) [158-P02EK381V4](#) [158-P02EK381V8](#) [158-P02EK381V6](#) [158-P02EK381V3](#)
[158-P02EK381V5](#) [158-P02EK381V2](#)