








FOR DISCRETE WIRE

FOR FLAT CABLE



NOTE
1. CONTACT PLATING
GOLD (0.2 μm) ON MATING AREA AND
TERMINATION AREA ALL OVER NICKEL.

2. PART NO.
PCS-E () PM ()
NO. OF POS.
CABLE CHARACTERISTICS

PART NO.	CABLE CHARACTERISTICS	
PCS-E () PMK	FOR DISCRETE WIRE	#30AWG (7/0.1) O. D. : 0.65~0.8
PCS-E () PMJ	FOR DISCRETE WIRE	#28AWG (7/0.127) O. D. : 0.65~0.8mm
PCS-E () PMD	FOR DISCRETE WIRE	#30AWG (7/0.1) O. D. : 0.5~0.65mm
PCS-E () PMC	FOR DISCRETE WIRE	#28AWG (7/0.127) O. D. : 0.5~0.65mm
PCS-E () PMB	FOR FLAT CABLE	#30AWG (7/0.1) THICKNESS: 1mm MAX.
PCS-E () PMA	FOR DISCRETE WIRE	#28AWG (7/0.127) O. D. : 0.8~1.0mm
PCS-E () PM	FOR FLAT CABLE	#28AWG (7/0.127) THICKNESS: 1mm MAX.

PCS-E68PM ()	68	63.9	57.9	46.28	1.27x33=41.91	52.1	52.1	PCS-E68PM
PCS-E50PM ()	50	52.5	46.5	34.85	1.27x24=30.48	40.7	40.7	PCS-E50PM
PCS-E36PM ()	36	43.6	37.6	25.96	1.27x17=21.59	31.8	31.8	PCS-E36PM
PCS-E28PM ()	28	38.5	32.5	20.88	1.27x13=16.51	26.7	26.7	PCS-E28PM
PCS-E20PM ()	20	33.4	27.4	15.8	1.27x 9=11.43	21.6	21.65	PCS-E20PM
PART NO.	N (NO. OF POS.)	A	B	C	D	E	F	MARKING (P/N)

X-X SECTION (5/1)

					6	CABLE COVER	PBT (GF)	2		UL94V-0 BLACK	
					5	SUPPORTER	PBT (GF)	2		UL94V-0 BLACK	
					4	INSULATOR	PBT (GF)	1		UL94V-0 BLACK	
△					3	SHELL	ZINC ALLOY	1	NICKEL PLATING		
△					2	CONTACT B	PHOSPHOR BRONZE	NO. OF POS./2	NOTE # 1		
△					1	CONTACT A	PHOSPHOR BRONZE	NO. OF POS./2	NOTE # 1		
LTR.	DATE	BY	REV.	DESCRIPT	No.	PART NAME	MATERIAL	QTY	FINISH	NOTE	
DATE		SCALE		UNIT	HONDA TSUSHIN KOGYO CO., LTD.						
JUL. 3, 1998		2/1		mm (INCH)							3RD. A. P
APP. DATE&REV.											
DR.	DE.	CHK.	CHK.	APP.	NAME		PCS-E TYPE MALE CONNECTOR (PANEL MOUNT)				
Y. OHKI	Y. OHKI	K. SATO	Y. HIRAI	H. MIYAZAKI	PART NO.		PCS-E () PM ()			REV.	