

REV.	ECN. NO.	DESCRIPTION

MATERIAL:

INSULATOR :Hi-temp PBT or PPS, UL 94V-0
 Contact material:phosphor bronze JIS 5210
 Contact Plated :120μ "tin over 30μ "nickel

SPECIFICATIONS:


Temperature range:-50℃ to 105℃
 CURRENT Rating :1 AMP
 Capacitance:1.0 Picoforads (Max)
 Contact resistance:30 Milliohms (Max)
 Insulation Resistance :1000 Megohms (Min)
 Withstanding Voltage: AC 600 Vrms

MIDDLE TYPE:

NO OF CONTACT	A±0.2	B±0.2	C±0.1	D±0.1	E±0.1	F±0.1
20 _{PBT} PPS	15.50	15.50	5.08	5.08	5.08	5.08
28 _{PBT} PPS	18.04	18.04	7.62	7.62	7.62	7.62
32 _{PBT} PPS	20.60	18.04	7.62	10.16	7.62	10.16
44 _{PBT} PPS	23.35	23.35	12.70	12.70	12.70	12.70
52 _{PBT} PPS	25.88	25.88	15.24	15.24	15.24	15.24
68 _{PBT} PPS	31.04	31.04	20.32	20.32	20.32	20.32
84 _{PBT} PPS	36.04	36.04	25.40	25.40	25.40	25.40
68 PBT	31.66	31.66	20.32	20.32	20.32	20.32
84 PBT	36.66	36.66	25.40	25.40	25.40	25.40

THIN TYPE:

NO OF CONTACT	A±0.2	B±0.2	C±0.1	D±0.1	E±0.1	F±0.1
44	23.35	23.35	12.70	12.70	12.70	12.70
68	31.04	31.04	20.32	20.32	20.32	20.32
84	36.04	36.04	25.40	25.40	25.40	25.40



Top Willing Co., Ltd.

圖名

DIP PLCC SOCKET


4000 Series

日期

2010-01-31

繪圖

CHENYIXIANG



UNIT/mm
 TOLERANCES (EXCEPT AS NOTED)
 MM 0.0±0.25 0.00±0.15
 INCH 0.00±0.01 0.000±0.006
 RADIUS ±0.25[0.010]
 HOLE ±0.13[0.005]
 ANGLES ±2°