




型番	STUD	H	被覆外径 D	型番	STUD	H	被覆外径 D
171512-1	#4	3.02	2.03~3.05	171512-7	#10	5	2.66~3.56
-2	#4	3.02	2.66~3.56	-8	#10	5	2.66~3.56
-3	#6	3.68	2.03~3.05	-9	5mm	5.26	2.03~3.05
-4	#6	3.68	2.66~3.56	1-171512-0	5mm	5.26	2.66~3.56
-5	#8	4.34	2.03~3.05				
171512-6	#8	4.34	2.66~3.56				

参考図面 (CUSTOMER CCQV, REFERENCE ONLY)			
AMP (JAPAN), LTD. Tokyo, Japan			
B1 OBSOLETE (F344-0515) K.N 4.7 6-23/93		B ADDED MARK H.D. H.N 7/1/75	
A REVISED (P-DWG) 71.5 H.C. 7/1/75		A RELEASED 8.4.58 7/1/75	
O (P-DWG REV. O) 8.4.58 7/1/75		LTR 変更 (REVISION RECORD) DR. CHK. DATE	
DR. 8.4.58 7/1/75		CHK. 8.4.58 7/1/75	
TOLERANCE EXCEPT AS NOTED ±0.4 ±1.0		R/S: SCALE, LOC SIZE S.C. NO.	
4-1		JAC-171512 B1	
丸型端子 RING TONGUE TERMINAL			