



BRIDGE RECTIFIERS, Surface Mount, Dual In Line

ISi Part Number	Maximum Average Rectified Current at T _a		Peak Inverse Voltage	Peak Forward Surge Current @ 8.3ms Superimposed	Max Forward Voltage @ Rated I _s and T _a =25°C	Max Reverse Current @ Rated PIV and T _a =25°C	Reverse Recovery Time @ Rated PIV	Pkg Quant	Outline
	I _s (Amps)	T _a (°C)	PIV (Volts)	I _{FSM} (Amps)	V _{FM} (Volts)	I _R (uA)	T _{RR} (nsec)	Tube/Reel	inches/millimeters
SDB101 SDB102 SDB103 SDB104 SDB105 SDB106 SDB107	1.0	40	50 100 200 400 600 800 1000	50	1.1	10	N/A	50 1500	 DBS
DF005S DF01S DF02S DF04S DF06S DF08S DF10S			50 100 200 400 600 800 1000						
EDF-1AMS EDF-1BMS EDF-1CMS EDF-1DMS			50 100 150 200						
				50	1.1	10	N/A	50 1500	 DFS