





STYLE I

8-321235-5	2.625	.860	NATURAL	CLEANED	I	LOOSE PC, BOX SPL	100	600	300
8-321235-1	2.625	.860	NATURAL	CLEANED		LOOSE PC, BOX	100	600	300
3-321235-0 	2.625	1.151	BLACK		I	LOOSE PC	1000		
1-321235-1	2.625	1.151	NATURAL		I	LOOSE PC	1000	600	300
1-321235-0	2.625	1.151	NATURAL	CLEANED		LOOSE PC	1000	600	300
321235	2.093	.860	NATURAL	CLEANED		LOOSE PC	1000	300	300
PART NO.	DIM 'A'	DIM 'B'	COLOR	FINISH	STYLE	PACKAGE TYPE	QTY	 FILE E66717  LR7189 Certified	
								MAX VOLTAGE RATING	

-  TIN PLATE PER ASTM B545.
-  PRELIMINARY - NOT FOR PRODUCTION.

WIRE SPLICE	SEE TABLE	INSULATION: PVC COLOR: SEE TABLE BODY: BRASS (ASTM B-19) .032 THK FINISH: SEE TABLE	
DESCRIPTION	PART NO.	MATERIAL & FINISH	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH		06OCT00		 TE Connectivity	
		CHK T MICHIELUTTI		06OCT00			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHIELUTTI		NAME	
		0 PLC ± -		PRODUCT SPEC		SPLICE, RECEPTACLE, FASTON, .250 SERIES WIRE SIZE: 22-10	
		1 PLC ± -		—			
		2 PLC ± -		APPLICATION SPEC		SIZE A2	
		3 PLC ± .008		—			
		4 PLC ± -		—		DRAWING NO C=321235	
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT —		RESTRICTED TO —	
CUSTOMER DRAWING						SCALE NTS	
						SHEET 1 of 1	
						REV U6	