

LOC	DIST	REVISIONS				
AJ	16	P	LTR	DESCRIPTION	DATE	DWN
		B1	REVISED	PER ECO-11-005030	11MAR11	RK

- 1

POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:NATURAL
- 2

POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3

ZINC PER QQ-Z-363.
- 4

PHOSPHOR BRONZE PER QQ-B-750.
- 5





BRASS PER ASTM-B-453.
- 6

NICKEL PLATE PER QQ-N-290, 3.81 μ m [.000150] MINIMUM THICK.
- 7


TIN PLATE PER ASTM-B-545, 3.81 μ m [.000150] MINIMUM THICK.
- 8

GOLD PLATE PER MIL-G-45204, 0.76 μ m [.000030] MINIMUM THICK.
9.

SEE INSTRUCTION SHEET 408-2769.



RECOMMENDED PANEL CUTOUT



PCB CONFIGURATION

	5226978-3
	5226978-1
CONTACT PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - 25APR2005	TE Connectivity		
		CHK J. HAVENER - 25APR2005			
DIMENSIONS: INCHES 	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. LIPPERT - 25APR2005	NAME JACK, RIGHT ANGLE, 50 OHM, PCB, SERIES BNC	
			PRODUCT SPEC 108-12078		
			APPLICATION SPEC		
			SIZE A1	CAGE CODE 00779	DRAWING NO C5226978
			RESTRICTED TO —		
MATERIAL SEE NOTES 1-5	FINISH SEE NOTES 6-9	WEIGHT —			
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	
			REV B		