






**HEADER STRAIGHT SOLDER PIN, 1X1  
MM / 0.039X 0.039 IN PIN SPACING 7.5  
MM / 0.295 IN 100% PROTECTED  
AGAINST MISMATING  
721-232/001-000 TO 721-242/001-000**

**PDF DATASHEET**

© 1992 - 2011 CADENAS GmbH

|                                                      |                                               |
|------------------------------------------------------|-----------------------------------------------|
| ITEM-NO. (ITEM-NO.)                                  | 721-232/001-000                               |
| Measured voltage (Measured voltage / V)              | 630                                           |
| Measured shock voltage (Measured shock voltage / kV) | 6                                             |
| Pollution degree (Pollution degree)                  | 2                                             |
| Current intensity (Current intensity / A)            | 12                                            |
| RM (PIN SPACING / mm)                                | 7.5                                           |
| P (NO. OF POLES)                                     | 2                                             |
| Height (Height / mm)                                 | 12                                            |
| Width (Width / mm)                                   | 15.5                                          |
| Depth (Depth / mm)                                   | 11.4                                          |
| COLOR (COLOR)                                        | lichtgrau                                     |
| WEIGHT (WEIGHT / g)                                  | 0.907                                         |
| Comment (Comment)                                    | A = (No. of poles - 1) x Pin Spacing + 8,2 mm |
| Dimensions (Dimensions)                              | 1,4 +0,1 mm                                   |