





注解


- 線 UL20276(30# 3C COAX)+(28#*1P+EAM)*4+28AWG*1P+28AWG*6C AEB
OD=8.5MM 外被顏色: 米色3#
- 連接器 J1-DVI 24+5C MALE SOLDER MD TYPE W/TS
J2-DVI 24+5C FEMALE(RIVET NUT) MD TYPE
J1,J2-(PIN針鍍金) 內部加箔隔離
W/"" LOGO ON THE PIN1~8 SIDE
- 螺絲 4*33.0MM(#4-40 UNC) 顏色: 米色3#
- 膠芯顏色: 黑色 外模成型PVC顏色: 米色3#
- 鐵粉芯(BRH15.5*28.5*10.5)
- 包裝 W/空白袋(右下角印"MADE IN CHINA")

PIN OUT		J1	J2
(1P+S)-1	1	XX	XX
	2	RED	2
	3	WHITE	3
(1P+S)-2	9	GREEN	9
	10	WHITE	10
	11	DRAIN WIRE	11
(1P+S)-3	17	BLUE	17
	18	WHITE	18
	19	DRAIN WIRE	19
(1P+S)-4	24	BROWN	24
	23	WHITE	23
	22	DRAIN WIRE	22
PAIR	C1	RED	C1
	C2	GREEN	C2
	C3	BLUE	C3
	C5	BRAIDING	C5(RED+GREEN+BLUE)
	6	YELLOW	6
SHELL	7	ORANGE	7
	8	BROWN	8
	C4	VIOLET	C4
	14	BLACK	14
	15	GREEN	15
	16	RED	16
	SHELL		SHELL



本圖繪之產品符合RoHs
環境管理物質的要求

G.W. NO.	LENGTH
HCD167200000000	2M±0.05M

1-0		AUG-16-2006	2214-060800006
REV	DESCRIPTION	DATE	ECN NO.
DWG NAME: DVI 24+5C M/F CABLE			
G. W. NO:	SEE THE TABLE	CUS. ID:	
CUS. NO:		DWG. NO:	DVI-126
SHEET:	1/1	TOLERANCE:	UNIT: mm
		. X	DRAW. BY:
		. XX	CHECKED
SCALE: 1:1		APPROVE	