

Item no.:	734-148
Product description:	HEADER STRAIGHT SOLDER PIN, 1X1 MM / 0.039X 0.039 IN 18 POLE PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING WITH CLOSED END MATING DIRECTION PERPENDICULAR TO PCB



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

Product group	3 (Multi Conn. System)
Weight	4.408 g
Color	light gray
pole count	18
Height	10.3 mm
Height	0.406 in
Width	65.4 mm
Width	2.575 in
Depth	8.5 mm
Depth	0.335 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A
Pollution degree	2
Measured voltage EN	320 V

Measured shock voltage	2.5 kV
Current intensity EN	10 A
Material group	I
Contact material	Electrolytic copper (Ecu)
Contact surface	tin-plated



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
734-148	ABS	04-HG469925/1-PDA	250	10	0,5-1,5
734-148	CCA	NL5641	250	10	0,5-1,5
734-148	CSA	154112-1465035	300	10	28-14
734-148	KEMA	2077592.02	250	10	0,5-1,5
734-148	UR	E45171	250	10	
734-148	UR	E45172	300	10	

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected