





MATERIAL NUMBER	OLD PART NUMBER	FINISH LENGTH
130013-0280	1R3G06A20A120	1.0'±.75-0 [.3M±19.1-0]

VOLTAGE RATING	600 VAC/VDC
AMPERAGE RATING	13A
PROJECTION	IP67
OPERATING TEMPERATURE	-20° C TO 105° C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E152210
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837



ITEM.	QTY.	COMPONENT	MATERIAL	FINISH
1	1	FLAG LABEL	PLASTIC FILM	BLACK/YELLOW
2	3	CONDUCTOR-16 AWG. 26X#30 COPPER STRANDING 600V	PVC	SEE WIRING DIAGRAM
3	1	RECEPTACLE SHELL	ALUMINUM	ANODIZED
4	3	CONTACT PIN	COPPER ALLOY	GOLD PLATED
5	1	3 POLE INSERT	PVC	YELLOW
6	1	POTTING	EPOXY	BLACK

CREATE DOC EEC NO: WNA2010-0423 DRAWN BY: 2010/01/08 CHKD BY: WOODMAN 2010/01/14 APPR: JFMURPHY 2010/01/14 REV DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
	▼=0 ▽=0	4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.013 ± --- 1 PLACE ± --- ± --- ANGULAR ±1/2°	IN/MM	2:1	INCH	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DRAWN BY: B. RUPERT 01/07/2010 CHECKED BY: B. WOODMAN 01/07/2010 APPROVED BY: JFMURPHY 2010/01/14	TITLE: MALE FLANGE RECEPT. MINI-CHANGE 3P 16AWG PVC MATERIAL NO. SEE CHART DOCUMENT NO. SD-130013-017			
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				