

HellermannTyton

DATA SHEET

HWPP: Helawrap

DESCRIPTION

The HWPP range of flexible harness protection is designed to protect cables when routed through areas where movement and vibration is experienced. The design allows a high degree of flexibility without the risk of crushing, creasing or splitting.

HWPP is available in a range of sizes and when used with 'zip action' applicators allows extremely fast routing and protection of cable looms.

HWPP is available in a size range of 8.0mm to 30.0mm inside diameters.

APPLICATION

To protect and route cables and harnesses in mass transit, panel building, aerospace and areas where post-termination protection is required quickly.

PROPERTIES

Properties	Typical Results	Test Method
Material	Polypropylene	
Continuous Operating Temp	-60°C to +110°C	IEC 216
Intermittent Temp	140°C	
Tensile Strength	27 MPa	ISO 527
Elongation	>50%	ISO 527
Flammability	HB (1.5mm)	UL94
Halogen Content	Halogen Free	
Shelf-life	5 years	
Colours	Black, White, Office Grey, Silver (others to order)	

STANDARDS


Approved to: N/A

Conforms to: N/A

Issue 5

Plymouth International Medical & Technology Park,
William Prance Road, Plymouth, Devon PL6 5WR, England
Telephone: +44 (0) 1752 701261; Fax: +44 (0) 1752 790058

10-2011



HWPP	A	W	P
8	8.0	0.70	10.0
16	14.0	0.80	13.0
20	19.0	0.95	16.0
25	24.0	1.05	20.0
30	30.0	1.30	24.0