





REV.	DATE	ECR NO.	DESCRIPTION
NC	02/02/09	—	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S

- NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .213" [5.41]
 2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068" [1.72]

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex									
7						DRAWN	GRS						02/02/09				
6						CHECKED			PART DESCRIPTION BNC R/A CRIMP PLUG (FOR RG-223/U, 400/U, 55/U, 142A/U)								
5						ISSUED											
4	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1		PART NO. 112725								
3	CONTACT PIN	BRASS	GOLD	1													
2	INSULATOR	PTFE	NATURAL	1				DWG. NO. 112725.DWG									
1	BODY	BRASS	NICKEL	1													
DESCRIPTION					MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		CAD FILE		C:/112/112725.DWG	REV. NC		SIZE A	SCALE NA	