



		REVISIONS				
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVE
✓			J	REDRAWN PER 0010-0226-96	3-96	ER/JH
✓			K	REY PER 0310-0389-97	12-97	CB/WJD
			K1	REVISED PER ECO-10-000445	22SEP09	HMR




Δ TOL. NON-CUMULATIVE.

2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



HOLE LAYOUT



FOR -1, -6, & -8

	OBSOLETE	102791-7	1.830	1.600	16	34	1-102792-1
	OBSOLETE	102791-5	3.130	2.900	29	60	1-102792-0
	OBSOLETE	102791-1	1.430	1.200	12	26	—
△		102991-2	.530	.300	3	8	—
		102791-3	.930	.700	7	16	—102792-7
		102991-1	.430	.200	2	6	102792-6
△	OBSOLETE	1-102791-0	1.130	.900	9	20	—102792-5
		102791-8	2.630	2.400	24	50	102792-4
	OBSOLETE	102791-6	2.130	1.900	19	40	102792-3
△	OBSOLETE	102791-4	1.030	.800	8	18	—102792-2
		102791-2	.630	.400	4	10	102792-1
	USED WITH PART NUMBER	C DIM	B DIM	A' SPACES	NUMBER OF POSITIONS	PART NUMBER	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .005 ANGLES ± .015 MATERIAL 155-FLAME RETARDANT THERMOPLASTIC COLOR- BLACK. POSTS- COPPER ALLOY	CONTRACT NO	AMP AMP INCORPORATED Harrisburg, Pa.		
	DR C. P. Brantner 3-25-96 CHK J. Harrington 3-26-96 APPO J. Harrington 3-26-96 APPO	NAME ASSEMBLY, HEADER, AMPMODU, DOUBLE ROW. 100 & RIGHT ANGLE		
FINISH POSTS: .000350 GOLD IN CONTACT AREA, GOLD FLASH ON REMAINDER OF POSTS, .000350 NICKEL UNDERPLATE	DSGN APPO	SIZE C	CODE IDENT NO 00779	DRAWING NO 102792
	OTHER APPO	SCALE 2-1	SHEET 1 OF 1	

CUSTOMER DRAWING