

Stratos

SPLC-20-2-4-Bx-R6 Optical Transceiver

Connectivity for
Business Critical Continuity™

Optical 1310nm LED Multimode SFP +3.3V



Product Overview

The Emerson Network Power Connectivity Solutions SPLC-20-2-4-BX-R6 pluggable transceiver module is a high performance integrated duplex data link for bi-directional communication over multimode optical fiber. It is compliant with the MSA Small Form Factor Pluggable (SFP) specification. The Stratos Lightwave SFP transceiver is hot pluggable which allows a suitably designed enclosure to be changed from one type of external interface to another simply by plugging in a SFP having the alternative external interface. The SPLC-20-2-4-BX-R6 operates at +3.3V. This optoelectronic transceiver module is a Class 1 Laser product compliant with FDA Radiation Performance Standards, 21 CFR Subchapter J. This component is also a Class 1 Laser compliant according to the International Safety Standard IEC-825-1. The SPLC-20-2-4-BX-R6 is provided with the 1310nm LED which provides highly reliable communications in excess of 2km.

Ordering Information

SPLC - 20 - 2 - 4 - B X - R6

Blank Actuator
BLANK=Commercial Temp Range
H=Extended Temp Range

Key Features & Benefits

- Fast Ethernet Compliant
- ESCON Compliant
- SONET OC-3/ST-1 Compliant
- Compliant with MSA SFP specification
- AC coupled Inputs/Outputs
- Hot pluggable
- Single +3.3V Power Supply
- Serial ID functionality
- RoHS compliant

Module Specifications – Electrical: +3.15V<Vcc<+3.45V

Parameter	Sym	MIN	Typ	MAX	Unit	Notes
Supply Current	Icc		180	250	mA	Tc = 25°C, Vcc = +3.3V
Surge Current	Isurge			300 30	mA	-40°C<Tc<+85°C; +3.15V<Vcc<+3.45V Surge above steady value
Transmitter						
PECL Inputs (Differential)		400		2400	mVpp	AC Coupled Inputs
Input Impedance (Differential)	Zin	95	100	105	Ω	Rin > 100KΩ @ DC
TX_DISABLE Input Voltage – High	ViH	2		3.45	V	
TX_DISABLE Input Voltage – Low	ViL	0		0.8	V	
TX_FAULT Output Voltage – High	VtoH	Vcc-0.5		Vcc+0.3	V	Io = 400μA; Host Vcc
TX_FAULT Output Voltage – Low	VtoL	0		0.5	V	Io = -4.0mA
Receiver						
PECL Outputs (Differential)		600	1200	1860	mVpp	AC Coupled Outputs
RX_LOS Output Voltage – High	VroH	Vcc-0.5		Vcc+0.3	V	Io = 400μA; Host Vcc
RX_LOS Output Voltage – Low	VroL	0		0.8	V	Io = -4.0mA
MOD_DEF (0:2)	VoH VoL	2.5 0		Vcc+0.3 0.5	V	With Serial ID

Stratos

SPLC-20-2-4-Bx-R6 Optical Transceiver

Connectivity for
Business-Critical Continuity™

Module Specifications – Optical: +3.15V<V_{cc}<+3.45V

Parameter	Sym	MIN	Typ	MAX	Unit	Notes
62.5µm Core Diameter SMF		2				BER<1.0E-12 @ 125Mbaud ¹ BER<1.0E-10 @ 155Mbaud ² BER<1.0E-15 @ 200Mbaud ³
Transmitter						
Optical Center Wavelength	λ	1280	1310	1360	nm	Tcase = +25°C
Optical Transmit Power	P _{opt}	-20		-14	dBm	Average @ 1310nm
Extinction Ratio	ER	10			dBm	P1/P0
Total Jitter [Pk – Pk]	T _j			800	ps	Measured with 2 ⁷ -1 PRBS ¹
Output Rise/Fall Time	t _r , t _f			3.2 1.7	ns	20%-80%; Measured unfiltered ¹ 20%-80%; Measured unfiltered ³
Receiver						
Optical Input Wavelength	λ	1270		1380	nm	
Optical Input Power	P _r	-31		-14	dBm	BER<1.0E-12 @ 125Mbaud PRBS 7 ¹ BER<1.0E-10 @ 155Mbaud PRBS 23 ² BER<1.0E-15 @ 200Mbaud PRBS 7 ³
RX_LOS – Asserted	P _a	-45			dBm	Measured on transition – Low to High
RX_LOS – Deasserted	P _d			-29	dBm	Measured on transition – High to Low
RX_LOS – Hysteresis	P _a -P _d		1.5	5	dB	

1. Fast Ethernet 125Mbps
2. SONET OC-3/STM-1 155Mbps
3. ESCON 200Mbps

For more information on this product consult the SPLC-20-2-2M-Bx-R6 product data sheet.

IMPORTANT NOTICE

Stratos International, Inc. reserves the right to make changes to or discontinue any optical link product or service identified in this publication, without notice. Stratos International, Inc. recommends that its customers obtain the latest version of the publications to verify, before placing orders, that the information being relied on is current. Stratos International, Inc. warrants performance of its optical link products to current specifications in accordance with the Stratos International, Inc. standard warranty. Testing and other quality control techniques are utilized to the extent that Stratos International, Inc. has determined it to be necessary to support this warranty. Specific testing of all parameters of each optical link product is not necessarily performed on all optical link products. Stratos International, Inc. products are not designed for use in life support appliances, devices, or systems where malfunction of a Stratos International, Inc. product can reasonably be expected to result in a personal injury. Stratos International, Inc. customers using or selling optical link products for use in such applications do so at their own risk and agree to fully indemnify Stratos International, Inc. for any damages resulting from such improper use or sale. Stratos International, Inc. assumes no liability for Stratos International, Inc. applications assistance, customer product design, software performance, or infringement of patents or services described here in. Nor does Stratos International, Inc. warrant or represent that a license, either expressed or implied is granted under any patent right, copyright, or intellectual property right, and makes no representations or warranties that these products are free from patent, copyright, or intellectual property rights. Applications that are described herein for any of the optical link products are for illustrative purposes only. Stratos International, Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.