








Date	Rev.	Description

ARRANGEMENT OF CONTACTS							SPECIFICATIONS
PARTS	3P	4P	5P	6P	7P	8P	Contact resistance 20M Ω Max.
ANGLE	180°	216°	180°	240°	270°	270°	Dielectric strength 1,000V AC/1 Minute
POSITION OF VIEWS							Insulation resistance 100M Ω Min. at 500V DC
							Rating 100V AC 2A



4	EARTH TERMINAL	1	BSR-H (0.2t)	[C1519R-H]	NICKEL	30-50U"
3	CONTACT TERMINAL	5	BSR-H (0.7t)	[C2680R]	SILVER PLATED	30-50U"
2	BASE	1	PBT	[D202G15]		UL94
1	MAIN BODY	1	PBT	[D202G15]		UL94
P/N	PART NAME	Q'TY	MATERIAL		PLATING ^o	REMARKS

DATE 980828 SCALE 2 : 1 UNIT M/M

5 P 180°
JACK

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
		JAMECO NO.	GOLDSUN NO.		
		29399	B-1001-R		
DRAWN: Colin Hung		Description	RIGHT ANGLE DIN FEMALE SOCKETS 5 PINS		Rev. 1
VERIFY PEOPLE: Penny		UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No:

DCC. NO.
A4 DRAWING NO.