



T18R8-0K2

Standard Cable Tie, 4" Long, 18lb Tensile Strength, PA66, Gray/Black Striped, 50/bag

Article Number: 111-01781

Part Number: T18R8-0K2

Type: T18R

Base Data

Part No.	T18R8-0K2
Type	T18R
Color	Gray (GY)
Features	• Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

Product Dimensions

Min. Tensile Strength	18.0lbs / 80.0N
Length (L)	4.0" / 100.0mm
Width (W) (imperial)	0.1"
Width (W)	2.45mm
Min. Ø Bundle	0.06" / 1.5mm
Max. Ø Bundle	0.86" / 22.0mm

Material and Specifications

Material	Polyamide 6.6 (PA66)
Flammability	UL94 V2

Material Specification	HF
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	 RoHS
Specification	UL ZODZ2.E64139
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	50
Carton Qty.	10000
EAN code	4031026433646
UPC	089306070375

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512