


D-SUBMINIATURE CONNECTORS:

KF22X Series

Right Angle PCB Mount 0.318" Footprint with Ferrite

KF22X Series Dimensions

Dimensions in mm



Shell Size	A	A1	B	C
In mm	±.010 ±.025	±.010 ±.025	±.005 ±.013	±.015 ±.038
9 (E)	.643 16.33	.666 16.92	.984 24.99	1.213 30.81
15 (A)	.971 24.66	.994 25.25	1.312 33.32	1.541 39.14
25 (B)	1.511 38.38	1.534 38.96	1.852 47.04	2.088 53.04
37 (C)	2.159 54.84	2.182 55.42	2.500 63.50	2.729 69.32

A = Exterior of Female Shell (S)
A1 = Interior of Male Shell (P)

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-				
Series		Shell Size Contact	Contact Type	Mounting Option	Plating Option

Series

KF22X - D-Subminiature Connector, 0.318" Footprint with Ferrite

Shell Size-Contact Option

E - 9 Contacts

A - 15 Contacts

B - 25 Contacts

C - 37 Contacts

Contact Type

P - Pin Contact (Plug)

S - Socket Contact (Receptacle)

Mounting Option

N - With Boardlocks and #4-40 UNC Threaded Inserts

NJ - With Boardlocks and #4-40 Jackscrews Installed

NR - With Boardlocks and #4-40 Round Jackscrews

Plating Option

Blank - Gold Flash

30 - 30μ" Gold

Contact Kycon for Other Options

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kycon:

[KF22X-B25S-NJ](#) [KF22X-A15P-N](#) [KF22X-A15S-N](#) [KF22X-B25P-N](#) [KF22X-A15P-NJ](#) [KF22X-E9P-N](#) [KF22X-C37P-N](#)
[KF22X-C37S-NJ30](#) [KF22X-C37S-N](#) [KF22X-C37S-NJ](#) [KF22X-B25S-N](#) [KF22X-B25P-NJ](#) [KF22X-C37P-NJ](#) [KF22X-A15S-NJ](#) [KF22X-E9P-NJ](#) [KF22X-E9S-N](#) [KF22X-E9S-NJ](#) [KF22X-B25S-NJM30](#) [KF22X-A15P-NJM](#) [KF22X-A15S-NT](#)
[KF22X-B25P-NJ15](#) [KF22X-A15P-NT](#) [KF22X-E9S-N15](#) [KF22X-E9P-NJM15](#) [KF22X-C37P-NR15](#) [KF22X-B25P-NJM30](#)
[KF22X-E9P-NJM](#) [KF22X-A15P-NJ30](#) [KF22X-A15P-NT15](#) [KF22X-A15S-NT30](#) [KF22X-C37S-NJ15](#) [KF22X-B25S-NT15](#) [KF22X-C37S-NR30](#) [KF22X-E9P-N15](#) [KF22X-C37S-N30](#) [KF22X-C37P-N30](#) [KF22X-B25P-NJ30](#) [KF22X-A15S-NR30](#) [KF22X-C37S-NJM](#) [KF22X-A15S-NJM30](#) [KF22X-E9P-NT](#) [KF22X-C37P-NJ15](#) [KF22X-B25P-NJM15](#) [KF22X-C37P-NR30](#) [KF22X-E9S-N30](#) [KF22X-A15S-N15](#) [KF22X-A15P-N15](#) [KF22X-B25S-NR15](#) [KF22X-C37S-NJM15](#)
[KF22X-E9P-N30](#) [KF22X-B25S-N15](#) [KF22X-C37P-NJM](#) [KF22X-B25P-NR](#) [KF22X-A15S-NJM15](#) [KF22X-A15P-NR](#) [KF22X-B25S-NR](#) [KF22X-A15P-NJ15](#) [KF22X-B25S-NJ15](#) [KF22X-B25S-NR30](#) [KF22X-B25P-NR15](#) [KF22X-E9P-NR15](#)
[KF22X-C37S-NJM30](#) [KF22X-B25P-NT30](#) [KF22X-C37P-NT15](#) [KF22X-C37P-N15](#) [KF22X-B25P-N30](#) [KF22X-A15S-NJM](#) [KF22X-C37P-NJM30](#) [KF22X-C37S-NT30](#) [KF22X-E9P-NT30](#) [KF22X-B25P-NT](#) [KF22X-E9S-NT](#) [KF22X-E9P-NR30](#) [KF22X-E9S-NJ15](#) [KF22X-C37P-NJM15](#) [KF22X-E9S-NJM15](#) [KF22X-A15S-NR15](#) [KF22X-C37P-NT30](#) [KF22X-C37P-NT](#) [KF22X-C37S-NT](#) [KF22X-A15P-NT30](#) [KF22X-E9P-NR](#) [KF22X-E9P-NJ15](#) [KF22X-E9P-NT15](#) [KF22X-B25S-NJ30](#) [KF22X-E9S-NR](#) [KF22X-A15S-NT15](#) [KF22X-E9P-NJ30](#) [KF22X-E9S-NJM](#) [KF22X-E9S-NJM30](#) [KF22X-C37P-NR](#) [KF22X-B25P-NR30](#) [KF22X-A15S-NJ15](#) [KF22X-B25S-NJM15](#) [KF22X-A15P-NR15](#) [KF22X-E9S-NT15](#) [KF22X-B25P-N15](#) [KF22X-B25S-NT30](#) [KF22X-C37S-NT15](#) [KF22X-B25P-NT15](#)