

main menu



home
 test & measurement
 products
 skills
 download

online catalogue T&M

clamp-type test probes
 crocodile clips
 test probes
 oscilloscope test probes
 measuring leads

plugs

sockets

- ▶ 2 mm system
- ▶ 2 mm safety system
- ▶ 4 mm system
- ▶ 4 mm safety system

sets

miscellaneous

company

portrait
 corporate association
 location maps
 fairs and exhibitions
 jobs
 imprint
 terms and conditions

Home ▶ sockets ▶ sockets ▶ PKI 110

PKI 110

datasheet for PKI 110
 article number: 931714101



View Full-Size Image



search online catalogue

Search

Search

Messetermine

No events

QR-Code



product description:	order number: 931 714-101
description:	Pole terminal with claw edge, captive insulated head and insulated ring. 4 mm diameter nickel-plated brass threaded bolt with 2 mm diameter transverse hole. For insulated, non-rotating installation in equipment chassis and switch panels up to 3.5 mm wall thickness.
typ:	PKI 110 rot/red
system:	4 mm system
order number:	931 714-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	4 mm socket (unsprung), 2 mm cross hole
type of termination:	M4 thread
rated voltage:	30 VAC / 60 VDC
rated current:	35 A
Please consider derating curve!	
contact resistance:	2 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	nickel
housing material:	PA
environmental conditions:	
temperature range:	-25 °C to +100 °C
flammable class:	
housing (basic material):	UL 94 V - 2
drawing	

