


[Home](#)[Products](#)[Distributors](#)[Technical](#)[Contact Us](#)[Other Options](#)

**Path:** [Home](#) > [Enclosure Index](#) > [ROLEC-HAMMOND Aluminum Product Index](#) > [Thick Wall](#) > **R101 Series**




### ***Key Features:***

- Material - Aluminum die-cast: G AI SI 12 / DIN 1775
- Deep lid, shallow body
- Captive stainless steel lid screws
- Neoprene oil and petrol resistant gasket standard. (-40°C up to +80°C)
- Degree of protection NEMA 4X, IP66, DIN 40050
- Temperature Range (-40°C up to +80°C)
- **Single-channel Fastening System.** Trouble-free turning 90° to 90° with square enclosures by synchronous arrangement of channels
- Special developed external mounting feet made from zinc-die-cast. Can be turned through 90°. The fastening holes have engagement lugs for this purpose. **(See accessories)**
- All sizes have inner blind holes. A mounting plate made of zinc-plated steel is available **(See accessories)**
- Textured polyester powder coat, light grey RAL7032. (can be supplied unpainted on special order)
- CSA certified, Type 4, for use with industrial control equipment

| Part No.     | Units  | Width | Length | Depth<br>(Including Lid) |
|--------------|--------|-------|--------|--------------------------|
|              |        | A     | B      | C                        |
| R101-080-000 | mm     | 80    | 80     | 60                       |
|              | inches | 3.2   | 3.2    | 2.4                      |
| R101-082-000 | mm     | 80    | 120    | 60                       |
|              | inches | 3.2   | 4.8    | 2.4                      |
| R101-084-000 | mm     | 80    | 160    | 60                       |
|              | inches | 3.2   | 6.4    | 2.4                      |
| R101-100-000 | mm     | 100   | 100    | 80                       |
|              | inches | 4     | 4      | 3.2                      |
| R101-102-000 | mm     | 100   | 150    | 80                       |
|              | inches | 4     | 6      | 3.2                      |
| R101-104-000 | mm     | 100   | 200    | 80                       |
|              | inches | 4     | 8      | 3.2                      |
| R101-120-000 | mm     | 120   | 120    | 100                      |
|              | inches | 4.8   | 4.8    | 4                        |
| R101-122-000 | mm     | 120   | 180    | 100                      |
|              | inches | 4.8   | 7.2    | 4                        |
| R101-124-000 | mm     | 120   | 240    | 100                      |
|              | inches | 4.8   | 9.6    | 4                        |
| R101-160-000 | mm     | 160   | 160    | 100                      |
|              | inches | 6.4   | 6.4    | 4                        |
| R101-162-000 | mm     | 160   | 240    | 100                      |
|              | inches | 6.4   | 9.6    | 4                        |
| R101-164-000 | mm     | 160   | 320    | 100                      |
|              | inches | 6.4   | 12.8   | 4                        |
| R101-166-000 | mm     | 160   | 480    | 100                      |
|              | inches | 6.4   | 19.2   | 4                        |
| R101-200-000 | mm     | 200   | 200    | 120                      |
|              | inches | 8     | 8      | 4.8                      |
| R101-202-000 | mm     | 200   | 300    | 120                      |
|              | inches | 8     | 12     | 4.8                      |
| R101-204-000 | mm     | 200   | 400    | 120                      |
|              | inches | 8     | 16     | 4.8                      |
| R101-240-000 | mm     | 240   | 240    | 120                      |
|              | inches | 9.6   | 9.6    | 4.8                      |
| R101-242-000 | mm     | 240   | 360    | 120                      |
|              | inches | 9.6   | 14.4   | 4.8                      |
| R101-244-000 | mm     | 240   | 480    | 120                      |
|              | inches | 9.6   | 19.2   | 4.8                      |
| R101-320-000 | mm     | 320   | 320    | 120                      |
|              | inches | 12.8  | 12.8   | 4.8                      |
| R101-322-000 | mm     | 320   | 480    | 120                      |
|              | inches | 12.8  | 19.2   | 4.8                      |

|                     |        |      |      |     |
|---------------------|--------|------|------|-----|
| <b>R101-324-000</b> | mm     | 320  | 640  | 120 |
|                     | inches | 12.8 | 25.6 | 4.8 |

## *Features (by photo):*



- 1** - Screws and mounting holes outside of gasket seal...
- 2** - Space saving single channel mounting (ie...same hole used for mounting enclosure through rear and for the lid), provides larger interior space than dual channel enclosures.
- 3** - Captive stainless steel lid screws...
- 4** - Enclosure holes threaded for easy installation and repetitive assembly & disassembly...
- 5** - Internal mounting shelves placed along both sides of enclosure include blind holes and grounding screws...

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check and ordering!!!

**Our Distributors**

[Order from your favorite distributor](#)

---

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)

---

Copyright; © 1999-2010 Hammond Mfg Co Inc

URL: <http://www.hammondmfg.com>