

Part Number **BRF.0K.200.NAS**

Size/Series 0K / K

[Request a quote](#)


MECHANICAL DETAILS

Shell Style/Model BRF*: Cap for free receptacle
Keying
Housing Material Brass (nickel plated) shell, collet nut, latch sleeve and mid pieces
Cable Fixing J : 0 - 0 mm
Variant :

PERFORMANCE DETAILS

OTHER CHARACTERISTICS

Endurance (Shell) 3839 mating cycles
Temp (min) -55°C deg
Temp (max) +200°C deg
Humidity (max): <=95% [at 60 deg C /140 F]
Vibration: 15 g [10 Hz - 2000 Hz]
Shock Resistance: 100 g [6 ms]
Salt Spray Corrosion: >144 hr
Climatical Category: 50/175/21
Shielding (min): 95 dB (10 MHz)
Shielding (min): 80 dB (1 GHz)
IP Rating 68
Catalog

[Copyright](#) [Privacy policy](#) [Product safety](#)

