





REV. 0
DCO 143831

COIL: @ 25°C	
RESISTANCE	720 OHMS ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	13.5 VDC
MUST RELEASE	8.1 VDC MAX., 1.5 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES:	
OPERATE 4 MS MAX.	
RELEASE 4 MS MAX.	
CONTACT STABILIZATION 2.5 MS MAX.	

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	LOW LEVEL TO
	2 AMPS 28 VDC RESISTIVE
	100,000 OPERATIONS

DR. B.D. 12NOV03

CK. 11/12/03

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/14-002M REV.

3SBH RELAY

3SBH1139A2